Part Number : 2064621200
Product Description : Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 12 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Series Number : 206462
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings
Drawing_2064621200_sd.pdf
Packaging Design Drawing_2064620000-PK-000.pdf

3D Models and Design Files
3D Model_2064621200_stp.zip

Specifications
Application Specification_2064600001-AS-000.pdf
Product Specification_2064600000-PS-000.pdf
Test Summary_2064600000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Accessories
Series	206462
Description	Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 12 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Component Type	Terminal Position Assurance
Product Family	Micro-Fit+ Connector System
Product Name	Micro-Fit+
UPC	191130009169

Agency

UL	E29179

Physical

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.217/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Use with Part(s)

Description	Part Number
Micro-Fit+ Dual Row Receptacle Housings	206461
Micro-Fit+ Dual Row Plug Housings	215922