KERN **357-04**

Individual weight, OIML Class M2, 10 g, Knob, stainless steel fine turned



Dimensions packaging (W×D×H)	24×24×51 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

Optional cases

Case - Plastic article number	347-050-400
Case - Aluminium article number	317-040-600
Case - Wood article number	337-040-200

Product information

GTIN/EAN number	4045761288959
REACH classification	no prohibited substances

Category

Brand	KERN
Product categoriy	Individual weight
Product group	OIML M2
Product family	357

Measuring System

Test weight - volume (cm^3)	1,1905
Test weight - Density uncertainty (kg/m^3)	140
Test weight - volume uncertainty (cm^3)	0,0241
Weight OIML class	M2
Test weight - nominal value	10 g
Permissible tolerance according to OIML (+/-)	6 mg
Test weight - Density (kg/m^3)	7950
OIML-compliant	✓

Construction

Shape weight	Knob
Dimensions (Ø×H)	10×17,5 mm
Material	stainless steel fine turned
Adjustment method	Polishing

Services (optional)

Article number for DAkkS calibration	962-634

Packing & Shipping

Delivery time	1 d

Pictograms

STANDARD

1 DAY

OPTION

DAkkS