ThinkCentre neo 50t 11SC000BGE

PERFORMANCE

Processor

Intel® Core™ i5-12400, 6C (6P + 0E) / 12T, P-core 2.5 / 4.4GHz, 18MB

Graphics

Integrated Intel UHD Graphics 730

Chipset

Intel B660

Memory 1x 16GB UDIMM DDR4-3200

Memory Slots

Two DDR4 UDIMM slots, dual-channel capable

Max Memory Up to 64GB DDR4-3200

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Support

Up to two drives, 1x 3.5" HDD + 1x M.2 SSD • 3.5" HDD up to 2TB • M.2 SSD up to 1TB

Optical

DVD±RW

Audio Chip

High Definition (HD) Audio, Realtek® ALC222-CG codec

Speakers

2Wx1

Power Supply

260W 90%

DESIGN

Keyboard USB Calliope Keyboard, Black, German

Mouse

USB Calliope Mouse, Black

Expansion Slots

- One PCIe 4.0 x16, full-height, half-length
- Two PCIe 3.0 x1, full-height, half-length
- Two M.2 slots (one for WLAN, one for SSD)

Case Color

Chassis: Black Bezel: Grey

System Fan

1x Rear

Form Factor Tower (13.6L)

Dimensions (WxDxH)

145 x 294 x 340 mm (5.71 x 11.57 x 13.39 inches)

Weight

5.5 kg (12.1 lbs)

CONNECTIVITY

Ethernet

Intel I219-V, 1x RJ45

Front Ports

- 2x USB 3.2 Gen 1
- 2x USB 3.2 Gen 2
- 1x USB-C 3.2 Gen 1 (support data transfer and 5V@3A charging)
- 1x headphone / microphone combo jack (3.5mm)

• 1x microphone (3.5mm)

- Rear Ports • 4x USB 2.0
- 4X USB 2
 1x VGA
- 1x VGA
 1x HDMI® 1.4b
- 1x DisplayPort[™] 1.4
- 1x serial (9-pin)
- 1x Serial (9-pill)
 1x Ethernet (RJ-45)
- 1x headphone (3.5mm)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified

Fingerprint Reader

No fingerprint reader

Physical Locks

Padlock Loop

Chassis Intrusion Switch

Chassis Intrusion Switch

MANAGEABILITY

System Management Non-vPro

SERVICE

- Base Warranty
- 1-year, Onsite Included Upgrade CO2 Offset 3 ton (5WS1C41958)

CERTIFICATIONS

PSREF

Product Specifications Reference

Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Gold
- EPEAT Silver
- TCO Certified 9.0
- RoHS compliant
- REACH
- WEEE

Other Certifications

TÜV Rheinland® Ultra Low Noise

SOFTWARE

Operating System

Windows® 11 Pro 64, German

MODEL

TopSeller	: Yes	Announce Date	: 2022-01-28
EAN / UPC / JAN	: 0196379950227	End of Support	: 2028-08-28



 \cdot Lenovo reserves the right to change specifications or other product information without notice.

 \cdot Product image on this page is a sample, it may not match the real color of this model

Premier Support - A direct 24x7x365 line to our most elite technicians.

Advanced technical support, 24x7x365, in more than 100 markets

Comprehensive hardware & OEM software support

Single point of contact for simplified end-toend case management

Technical Account Managers for proactive relationship and escalation management

Priority on service delivery and repair parts

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

· Pick Up & Return Courier

Technician Installed Customer

Onsite Support

- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

Lenovo Powered USB-C Travel Hub

Travel-Ready Productivity Powerhouse: One-stop travel docking is finally here. Connect and charge new and legacy devices wherever you happen to be. Sleek and compact, the Lenovo Powered USB-C Travel Hub fits unlimited...

Recommended Services

BEST	5Y Premier Support Upgrade from 1Y Onsite (5WS0T36190)	
BETTER	4Y Premier Support Upgrade from 1Y Onsite (5WS0T36168)	
GOOD	3Y Onsite upgrade from 1Y Onsite (5WS0D80967)	

For a full list of accessories and services, please visit: https://smartfind.Lenovo.com

PSREF **Product Specifications** Reference