KERN **YKA-12**

Power adapter (EU/UK/US)



Category

Brand	KERN
Product categoriy	Balance
Product group	Power adapter

Measuring System

Internal measuring frequency	60 Hz

Construction

Dimension (W×D×H)	70×50×45 mm
Material	plastic

Power Supply

Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V, 800 mA
Power socket for mains adapter	Hollow plug, inside plus, outside 3,5 mm, inside 1,5 mm

Approval

CE mark	✓

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	90×80×50 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,20 kg
Shipping weight	0,167 kg

Product information

GTIN/EAN number	4045761178373
REACH classification	no prohibited substances

Pictograms

STANDARD

