

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: Mextronic

Supplier's address: DELYCHI GMBH, Schreiberstr. 16D, 47058 Duisburg, DE

Model identifier: LT5050W606050024IP44

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	Wire		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Yes

Product parameters


Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	7	Energy efficiency class	F
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	750 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	6 000
On-mode power (P_{on}), expressed in W	7,2	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	82
Outer dimensions without separate control gear, lighting control	Height	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width		
	Depth		

parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-	
		Chromaticity coordinates (x and y)	0,315 0,306	
Parameters for LED and OLED light sources:				
R9 colour rendering index value	4	Survival factor	1,00	
the lumen maintenance factor	0,96			

(a) : not applicable;


(b) : not applicable;

Spectrum



Spectral Distribution

Model placed on the Union market from 05/03/2021



EPREL registration number: 907871

<https://eprel.ec.europa.eu/qr/907871>

Supplier: DELYCHI GMBH (Manufacturer)

Website: www.mextronic.de

Customer care service:

Name: DELYCHI GMBH

Website: www.mextronic.de

Email: info@delychi-gmbh.de

Phone: +49 203 51881370

Address:

Schreiberstr. 16D

47058 Duisburg

Germany