KERN **YKA-45**

Mains adapter 100 V - 240 V, 50 / 60 Hz, standard EURO/US/AUS/UK/CH

Category

Brand	KERN
Product categoriy	Balance
Product group	Power adapter

Construction

Material	plastic

Power Supply

Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V, 1 A
Power socket for mains adapter	Hollow plug, inside minus, Ø inside 2,1 mm, Ø outside 5,5 mm, long 12 mm

Environmental conditions

Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	90×70×70 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,15 kg
Shipping weight	0,133 kg

Product information

GTIN/EAN number	4045761239821
REACH classification	no prohibited substances

Pictograms

STANDARD

