WAVLINK

see the world

Quick Start Guide

Wi-Fi 7 BE3600 Dual Band Gigabit Mesh Router

kb.wavlink.xyz/docs/Skyline-Stream4/v100/

Connect to the Link to View the Detailed User Guide

WAVLINK (@WavlinkOfficial)
WAVLINK SUPPORT (@WavlinkTechSupport)

Skyline Stream 4

Overview



❶ 2.4 Antenna ❷ 5G Antenna



❸ 3×Gigabit LAN Port ❹ 1×Gigabit WAN Port
❺ PAIR/RESET ❻ DC IN

Basic Info

2.4G SSID: WAVLINK-Mesh_XXXX
5G SSID: WAVLINK-Mesh_XXXX
Default IP: 192.168.20.1
Login: http://wavlogin.link

LED Indication

Mode	LED Status	Description
Router Mode	Solid on	The Internet connected
	Fast blinking	No Internet connected
	Slow blinking	In pairing
Repeater Mode	Solid on	The Internet connected
	Slow blinking	Upper router connected but the Internet disconnected
	Fast blinking	Upper router disconnected
AP Mode	Solid on	The Internet connected
	Fast blinking	No Internet connected
	Slow blinking	In pairing

Note:
Press the RESET/PAIR button for more than 6 seconds then the light is solid on. Press the RESET/PAIR button for 2s, the LED will be slow blinking.

Router Mode Wizard

1. Connect this router's WAN port to the Modem's or others' LAN port, then connect the DC IN to the power outlet, turn on this router.



2. Connect your PC/Laptop to the router using the Ethernet cable or WiFi.

2.1 Using Ethernet Cable

2.1.1 Turn off the WiFi on your computer, then connect the computer to the LAN port of the router.



2.2 Using Wi-Fi

2.2.1 Find the SSID(Network Name) printed on the label at the bottom of the router.

2.2.2 Click the network icon of your computer or go to Wi-Fi Settings of your computer/phone, and then select the SSID(Network Name) to join the network.

For Windows Users

For Mac Users

3.Launch a browser from your computer or smart phone and enter http://wavlogin.link in the address field not search bar. Follow the Detailed Guide to finish the configuration.

For the guide of Repeater, AP mode configuration and other functions, please scan the QR code on the cover for the detailed guide.

FAQ

Q1. Why doesn't the login page appear after entering http://wavlogin.link ?
- Please make sure your computer is set to obtain an IP address automatically.
- Verify if http://wavlogin.link is correctly entered in the web browser.
- Use another web browser and try it again.
- Reboot your router and try it again.

Q2. What can I do if I cannot access the Internet?
- Please check if the Internet is working normally by connecting a computer directly to the modem with an Ethernet cable. If it is not, contact your internet service provider.
- Open a web browser, enter http://wavlogin.link and run the quick setup again.
- Reboot your router and try again.

Q3. How can I restore the router to its factory default settings?
- While the router is powered on, press and hold the RESET button of the back for more than 6 seconds.

Q4. What can I do if I forget my Administration Management password?
- Refer to FAQ > Q3 to reset the router.

Q5. What can I do if I forget my wireless network password?
- Log in the router's web management page at http://wavlogin.link and go to Wireless, you can find your Wi-Fi password here.

Q6. How to deploy the router to get the best Wi-Fi signal?
- Keep the router in the most central spot in your home and away from anything that might block its signal.

GNU General Public License Notice

This product includes software codes developed by the third parties. These software codes are subject to either the GNU General Public License (GPL), Version 2, June 1991 or the GNU Lesser General Public License (LGPL), Version 2.1, February 1999. You can copy, distribute, and/or modify in accordance with the terms and conditions of GPL or LGPL. The source code should be complete. If you want us to provide any additional source code files under GNU General Public License (GPL), please contact us in these matters. We are committed to meeting the requirements of the GNU General Public License (GPL). You are welcome to contact our local office to get the corresponding software and licenses. Please inform us your contact details (full address) and the product code. We will send you a software package with the software and license for free. The respective programs are distributed WITHOUT ANY WARRANTY, without even the implied warranty of MERCHANTABILITY or FITNESS FOR A PARTICULAR PURPOSE. Please refer to the GNU General Public License Website for further information.
http://www.gnu.org/licenses/old-licenses/lgpl-2.0.html
http://www.gnu.org/licenses/gpl.html

WEEE Directive & Product Disposal

At the end of its serviceable life, this product should not be treated as household or general waste. It should be handed over to the applicable collection point for the recycling of electrical and electronic equipment, or returned to the supplier for disposal.

Need help?

We're here for you!

Online support: wavlink.com
Available Mon-Fri 8:30 am-5:30pm (UTC+8)

support@wavlink.com
Available Mon-Fri 8:30 am-5:30pm (UTC+8)

+1 8889730883 (US Local)
Mon-Fri 9:00 am - 10:00 pm (UTC-5)

www.wavlink.com

Thank you for purchasing WAVLINK product!

WN530BE1-A说明书WAVLINK-E1
105g铜版纸四色印刷，正反印，风琴折
产品尺寸72X106mm 展开尺寸288*106mm