

New Fluke TL175 TwistGuard™ Test Leads

Twist. Test.

Technical Data


TL175 TwistGuard™ Test Leads offer:

- Patented TwistGuard™ extendable tip shroud that meets new electrical safety requirements to reduce tip exposure while providing the versatility needed for most measurements
- New WearGuard™ lead wire wear indicator. Each test lead is covered by two layers of silicone insulation; inner contrasting color is exposed when the leads are nicked, scuffed, or otherwise damaged and in need of replacement
- Double insulated silicone leads. TL175 withstands high temperatures and remains flexible in cold temperatures
- Extra-heavy strain relief on both probe-end and plug-end, tested beyond 30,000 bends without failure
- Universal input plugs compatible with all instruments that accept standard 4 mm shrouded banana plugs
- Probes always show correct category rating for tip exposure being used
- TL175E also available. Includes removable 4 mm lantern tips for versatility
- Conforms to EN61010-031
- Ratings: CAT II 1000 V, CAT III 1000 V, CAT IV 600 V, 10 A max., Pollution Degree 2
- Environmental ratings: -20 °C to 55 °C (-4 °F to 131 °F), altitude: 2000 m (6,562 ft)

The Fluke TL175 TwistGuard™ Test Leads offer adjustable length test tips for use in different measurement environments. By simply twisting the test lead the user can change the exposed probe tip length from 19 mm to 4 mm (0.75 in to 0.16 in).



TL175 TwistGuard™ Test Leads



Reduce tip exposure for accurate placement



Extreme strain relief tested to withstand over 30,000 bends




Increase tip exposure for CAT II probing



Universal plugs compatible with all 4 mm shrouded inputs



Reduce tip exposure for CAT III testing



WearGuard™ indicator shows insulation damage

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or
Fax (425) 446-5116
In Europe/M-East/Africa +31 (0) 40 2675 200 or
Fax +31 (0) 40 2675 222
In Canada (800)-36-FLUKE or
Fax (905) 890-6866
From other countries +1 (425) 446-5500 or
Fax +1 (425) 446-5116
Web access: <http://www.fluke.com>

©2010-2012 Fluke Corporation.
Specifications subject to change without notice.
Printed in U.S.A. 5/2012 3860288C_EN

Modification of this document is not permitted without written permission from Fluke Corporation.

Ordering information

Model
TL175 TwistGuard™ Test Leads