
DATASHEET

USB-A 2.0 Receptacle (Female connector)

Item No. 3385888

Overview



Pin definition	
Function	P.C.B
VCC	1
D−	2
D+	3
GND	4

Technical data

Rated current.....1.5 A
Rated voltage .....5 V
Nominal voltage.....30 V
Protection level.....IP67
Temperature range .....-25 to 80 °C
Insertion and removal times .....≥500
Connection type.....USB-A
Connection A.....USB 2.0 socket A
Connection B.....Pin header
Contact material .....Copper alloy
Housing material.....PA



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2025 by Conrad Electronic SE.