
DATASHEET

USB-C® 3.0 Waterproof cable (Male to Female)

Item No. 3385899

Overview



Pin Assignment		
P1	Wire Color	P2
A4.A9 B4.B9	Red	A4.A9 B4.B9
A7	White	A7
A6	Green	A6
A1.A12 B1.B12	Black	A1.A12 B1.B12
B10	Orange	B10
B11	violet	B11
A5	Yellow	A5
B5	Blue	B5
A3	Yellow	A3
A2	Blue	A2
Shell	Shield Braid	Shell

Technical data

Rated current.....3 A
Rated voltage.....20 V
Nominal voltage.....30 V
Protection level.....IP67
Temperature range.....-25 to 80 °C
Insertion and removal times.....≥500
Cable length.....0.5 m
Connection type.....USB-C®
Connection A.....USB-C® 3.0 socket
Connection B.....USB-C® 3.0 connector
Cable diameter.....4.35 - 4.65 mm
Contact material.....Copper alloy
Housing material.....PA



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2025 by Conrad Electronic SE.