
DATASHEET

RJ45 Receptacle CAT6A (Female to Female)

Item No. 3385913

Overview



Technical data

Rated current.....1.5 A
Rated voltage .....48 V
Protection level.....IP67
Temperature range .....-25 to 80 °C
Insertion and removal times .....≥500
Connection type.....RJ45
Connection A.....RJ45 socket
Connection B.....RJ45 socket
Contact material .....Copper alloy



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2025 by Conrad Electronic SE.