MATERIALS AND FINISHES

SMA PLUG: (73251-4980)
SEE SD-73251-498

SMP JACK: (73406-6680)
SEE SD-73406-668

CABLE:
TEMP-FLEX 100054-0006

LABEL:
BRADY PERMASLEEVE

SHRINK TUBE:
VERSAFIT OR EQUIVALENT



PART NO.	INCH	MM	INSERTION LOSS MAX TO 26 GHz (dB)
	DIM A		
89762-1403	120.0±2.00	3048±50.8	10
89762-1402	12.00±.25	304.80±6.35	1.45
89762-1401	9.00±.15	228.6±3.8	1.07
89762-1400	6.00±.15	152.4±3.8	0.7

PRE-RELEASE REFERENCE USE ONLY

MAX VSWR 1.50 @ 26 GHz

QUALITY SYMBOLS
FA = 0
FC = 0
FP = 0
▼ = 0
C = 0
☒ = 0
■ = 0
E = 0

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

EC NO: 107613 2016/08/22
DRWN: PSWAMI02 2016/09/14
CHK'D: PSWAMI02 2016/09/14
APPR: AROBERTSON 2016/09/14
REV B

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	± 0.01	±
2 PLACES	±	± 0.25
1 PLACES	±	±
0 PLACES	±	±

ANGULAR TOL ±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION UNITS: INCH
SCALE:
DRWN BY: LMEIER DATE: 2016/02/26
CHK'D BY: DATE:
APPR BY: AROBERTSON DATE: 2016/02/29
DRAWING SIZE: C
THIRD ANGLE PROJECTION

molex®

CA SMA P STR / SMP J STR
100054-0006 CABLE PT-10010-A, CA-SMA/SMP

PRODUCT CUSTOMER DRAWING

SERIES	MATERIAL NUMBER	CUSTOMER
89762	SEE TABLE	

DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
SD-89762-140	PSD	000	1 OF 2

RELEASE STATUS | RELEASE DATE

FORMAT: IN-master-lb-prod-C
REVISION: B
DATE: 2016/02/02