Antec

CX500M ARGB
CX500M ARGB WHITE

Mini-Tower Gaming Case

PANORAMIC 270° VIEW

Standing out with full-view design on the seamless steel-tempered glass, CX500M ARGB's left and front panel offer an unobstructed view of your build, creating a stunning showcase for your components.

VERTICAL COOLING WITH MASSIVE AIR INTAKE

Bottom-up vertical airflow via mesh on lower front, lower left, and right side accelerates the heat dissipation.


1.5mm
Right Side


STUDS FOR FIXING

TOOL-FREE PANELS

Front and side panel adopt fixing stud design, which makes assembly and disassembly easier and helps avoid possible glass breakage.


REAR
1 x 120mm ARGB fan
SIDE
2 x 120mm ARGB
REVERSE fans

PRE-INSTALLED
3 X 120MM ARGB FANS

Use the major case fan to daisy-chain the other two fans for ARGB sync and create your personal style.


FAN INSTALLATION
MB
1 x 120mm ARGB
Major Fan (Rear)
2 x 120mm ARGB
Secondary Fans (Side)

360mm
Radiator

SUPPORT TOP 360MM WATER COOLER

I/O PANEL


Type-C 3.2
Gen 2
USB 3.0
Headphone/Mic
Combo Jack
LED Control
Power

FULL REUSABLE PCI SLOT COVERS

Reusable PCI slot covers fulfill an optimal build experience.



EVA PSU CUSHION PADS

With EVA anti-vibration foams on the power supply mount position, your lovely PC hardware is well protected against any jar or resonance caused by PSU operation.

UP TO 9 FANS SIMULTANEOUSLY


TOP
3 x 120mm / 2 x 140mm
Fans Compatibility
REAR
1 x 120mm
POWER SUPPLY SHROUD
3 x 120mm
SIDE
2 x 120mm
TOP
Up to 360mm Radiator
Radiators Compatibility

POWERFUL AIR COOLING COMPATIBILITY

Max. CPU Cooler Height: 165mm

COMPATIBILITY

Motherboard support	Micro-ATX , ITX
CPU cooler max height	≤ 165mm
GPU max length	≤ 415mm
2.5"	1
3.5" / 2.5" Drive Mounts	2 / 1
Power Supply max length	(Include cable) ≤ 210mm (With HDD) (Not Include cable) ≤ 270mm (Without HDD)


Motherboard
CPU
GPU
SSD
HDD / SSD
HDD
Power Supply

SUPPORT LENGTHY RTX 40 SERIES GPU

Max GPU Length: 415mm

AMPLE CABLE MANAGEMENT SPACE

23mm of cable management space enusres your PC build looks neat.



DIMENSIONS

436 x 210 x 446mm (DWH)


210mm
436mm
446mm

SPECIFICATIONS

Main Spec

Motherboard Support	Micro-ATX , ITX
Form Factor	Mini Tower
Case Material	Steel + Glass
Side & Front Panel	4mm Tempered Glass
I/O Ports	Power, LED Control, USB3.0 x 2, Type-C 3.2 Gen 2 x 1, Headphone/Mic Combo Jack

Compatibility & Clearances

CPU Cooler Max Height	≤ 165mm
GPU Max Length	≤ 415mm
Power Supply Max Length	(Include cable) ≤ 210mm (With HDD) (Not Include cable) ≤ 270mm (Without HDD)
Cable Routing Space	≤ 23mm

Fan Support

Top	3 x 120mm / 2 x 140mm
Side	2 x 120mm
Power Supply Shroud	3 x 120mm
Rear	1 x 120mm

Radiator Support

Top	120/140/240/280/360mm

Expansion Slots

Standard	5

Drive Bays

2.5"	1
3.5" /2.5"	2/1

Dimensions

Case Dimensions	436 x 210 x 446mm (DWH)
Box Dimensions	505 x 290 x 520mm (DWH)
Net Weight	6.34kg
Gross Weight	8.2kg

Accessories

Included Fans	2 x 120mm ARGB reverse fans on right side + 1 x 120mm ARGB fan in rear

General

Dust Filter	Top / Bottom
Warranty	1 year
UPC#	0-761345-10143-1 CX500M ARGB 0-761345-10144-8 CX500M ARGB White

Antec