364

0% MERCURY

SR621SW (SR60)
Watch Battery
Swiss Made

Technical Data Sheet


Specifications

Chemical system	Zinc / Monovalent Silver Oxide, low drain
Nominal Voltage	1,55 V
Capacity	19 mAh, Discharge over 47,0 kΩ at 20°C to 0,9 V
Operating Temperature*	-10°C – 60°C
Self Discharge	Less than 5% per year at 20°C
Weight	~0,30 g

Dimensions


(according IEC 60086-3)

Diameter	6,80 mm (0,268“)
Height	2,15 mm (0,085“)



Discharge Curve

Constant Load	47,0 kΩ
Starting Drain	33 µA
Temperature	20°C



**Condensing humidity not allowed*

Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the PSDS document related to that product or product family. The Products of Renata SA are neither designed nor authorized for use in certain areas of application of environment. For further details we refer to our webpage www.renata.com/downloads/restriction_of_use

Rev. 364MF.04 2019/08

Renata SA
CH-4452 Itingen/Switzerland
Tel. +41 (0)61 975 75 75
Fax. +41 (0)61 975 75 95
sales@renata.com
www.renata.com

A COMPANY OF THE SWATCH GROUP