
DATASHEET

Push Button Switch

Overview



All dimensions in mm

Technical data

Item No.	Function	Operation type	Mechanical Life	LED Colour
3734941	Momentary	1NO1NC	1,000,000	Red
3734944	Momentary	1NO1NC	1,000,000	Green
3734945	Momentary	1NO1NC	1,000,000	Blue
3734946	Momentary	1NO1NC	1,000,000	White
3734947	Latching	1NO1NC	500,000	Red
3734948	Latching	1NO1NC	500,000	Green
3734949	Latching	1NO1NC	500,000	Blue
3734950	Latching	1NO1NC	500,000	White
3734951	Momentary	2NO2NC	1,000,000	Red
3734952	Momentary	2NO2NC	1,000,000	Green
3734953	Momentary	2NO2NC	1,000,000	Blue
3734954	Latching	2NO2NC	500,000	Red
3734955	Momentary	2NO2NC	1,000,000	White
3734956	Latching	2NO2NC	500,000	Green
3734957	Latching	2NO2NC	500,000	White
3734958	Latching	2NO2NC	500,000	Blue

Switch rating ..... 3 A / 250 VAC
Mounting diameter ..... 22 mm
Head shape ..... Round flat head
Illumination type ..... Ring illumination
Illumination voltage ..... 12 V
Terminal ..... Pin terminal (2.8 X 0.5 mm)
Operating conditions ..... -25 to +55 °C, 45 - 85 % RH
Storage conditions ..... -25 to +55 °C, 45 - 85 % RH
Material ..... Stainless steel
Electrical life ..... 50,000 cycles
Dielectric strength ..... 1,500 V, RMS 50 Hz, 1 min.
IP degree IP65

Case / button color ..... Silver
Transitional resistance ..... ≤ 50 mΩ
Panel thickness (max.) ..... 8 mm
Dimensions (L x W x H) ..... 34.5 x 25 x 25 mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.