
DATASHEET

Push Button Switch

Overview



All dimensions in mm

Technical data

Item No.	Function	Operation type	Mechanical Life
3734959	Momentary	1NO1NC	1,000,000
3734960	Momentary	2NO2NC	1,000,000
3734961	Latching	1NO1NC	500,000
3734962	Latching	2NO2NC	500,000

Switch rating.....3 A / 250 VAC
Mounting diameter.....22 mm
Head shape.....Round flat head
Illumination type.....Ring illumination
Illumination color.....RGB (common cathode)
Illumination voltage.....12 V
Terminal.....Pin terminal (2.8 X 0.5 mm)
Operating conditions.....-25 to +55 °C, 45 - 85 % RH
Storage conditions.....-25 to +55 °C, 45 - 85 % RH
Material.....Stainless steel
Electrical life.....50,000 cycles
Dielectric strength.....1,500 V, RMS 50 Hz, 1 min.
IP degree.....IP65
Case / button color.....Silver
Transitional resistance.....≤ 50 mΩ
Panel thickness (max.).....8 mm
Dimensions (L x W x H).....34.5 x 25 x 25 mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.