
DATASHEET

Pushbutton switch



All dimensions in mm

8MAX: means the panel thickness, the max thickness for the panel no more than 8 mm.

Technical data

Mounting diameter ..... 8 mm
Head shape ..... Round head
Operation type ..... Momentary / Latching
Contact structure 1NO1NC
Switch rating ..... 0.5 A / 250 V/AC
Terminal ..... Pin terminal
Operating and storage temperature ..... -25 to +55 °C
Operating and storage humidity ..... max. 85 % RH
IP rating IP40

Item no.	Function	Head Color
3734997	Momentary	Red
3734996	Momentary	Green
3734994	Momentary	Blue
3734999	Latching	Red
3734998	Latching	Green
3735000	Latching	Blue

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.