DATASHEET

Rocker On/Off Switch, Connection Type-C 7/16 plug, IP65




Item no.: 3747153



Item no.: 3747154

UNIT: MM



Technical data

Casing/button Colour	3747153: Black and Orange 3747154: Black and Blue
Functions	Latch
Bulb type	Glow lamp
Connection	Type-C CEE 7/16 plug 6.3 mm
Nominal voltage	250 V/AC
Nominal current	16 A
Front panel thickness	2 mm
Front panel cut-out	22 x 30.2 mm
IP rating	IP65
On/Off switch	2
Mechanical life	300,000 switching cycles
Tempureature range	-10 to +80 °C
Lighting type	LED
Colours (LEDs)	3747153: Orange 3747154: Blue
Print motif	0/I
Material	Thermoplastic
Contact material	Cu-alloy, nickel plated
Contact resistance	≤100 mΩ
Insulation resistance	≥100 MΩ
Number of pins	4
Dielectric strength	≥1500 V AC / 5 mA / 5 s
Dimensions (L x W x H)	38 x 29 x 40.5 mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.