DATASHEET

Electromagnetic switch


Technical data


Item No.:	3770818	3770819	3770820	3770821	3770822	3770823	3770824	3770825	3770826
Model No	DZ08-4B6	DZ08-4C6	DZ08-4D6	DZ08-8	DZ-6-2M	DZ05	DZ08-2B3	DZ08-2C3	DZ08-2D3
Cable	Yes	Yes	Yes	No	No	No	Yes	Yes	Yes
Cable type	H07RN-F 5G1.5 mm^2	H07RN-F 5G1.5 mm^2	H07RN-F 5G1.5 mm^2	N/A	N/A	N/A	H07RN-F 3G1.5 mm^2	H07RN-F 3G1.5 mm^2	H07RN-F 3G1.5 mm^2
Cable lenght	67 cm	67 cm	67 cm	N/A	N/A	N/A	67 cm	67 cm	67 cm
Rated Voltage	400 V	400 V	400 V	400 V	250 V	400 V	250 V	250 V	250 V
Rated Current	12A	12A	12A	12A	15 A	10 A	16 A	16 A	16 A
AC-3	12 A	12 A	12 A	12 A	15 A	10 A	16 A	16 A	16 A
AC-15	6 A	6 A	6 A	6 A	-	-	8 A	8 A	8 A
Protection Level	IP54	IP54	IP54	IP54	IP55	IP55	IP54	IP54	IP54
CEE Collar Plug	3P+N+E	3P+N+E	3P+N+E	N/A	N/A	N/A	2P+E	2P+E	2P+E

Colour.....Black / red / yellow
Material.....PA66
Rated frequency.....50 Hz
Max. ambient temperature.....T55
Number of operating cycles.....50000


Overview


Item no: 3770818







Item no.: 3770819










Item no.: 3770820










Item no.: 3770821













Item no.: 3770822














Item no.: 3770823















Item no.: 3770824













Item no.: 3770825













Item no.: 3770826









This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.