
BU-4150081XXX

(Cable Assembly Coaxial SMA Straight to SMA Straight Male to Male RG-086, Hand-Formable)





Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524

Electrical Ratings

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

Connector	Cable	Connector Impedance (Ohms)	Frequency (GHz)	VSWR	Working Voltage (At Sea Level)
SMA	RG-086	50	DC-18	1.3 MAX	335V

Product Attributes

Gender	Male to Male
Style	SMA to SMA
1st Connector	Gold Plated SMA Male Plug Straight
2nd Connector	Gold Plated SMA Male Plug Straight
Features	Shielded
Operating Temperature	-65°C (-85°F) to 150°C (302°F)
BU-4150081003 BU-4150081004 BU-4150081005 BU-4150081006 BU-4150081007 BU-4150081008 BU-4150081012 BU-4150081018 BU-4150081024 BU-4150081MM150 BU-4150081MM750	3” (76.2 mm) 4” (101.6 mm) 5” (127 mm) 6” (152.4 mm) 7” (177.8 mm) 8” (203.2 mm) 12" (304.8 mm) 18” (457.2 mm) 24" (609.6 mm) 150mm (5.9”) 750mm (29.5”)
RoHS 3 Compliant	