
BU-4150088XXX

(Cable Assembly Coaxial U.FL Female to U.FL Female 1.37mm Ø Cable)





Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524

Electrical Ratings

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

Connector	Cable	Connector Impedance (Ohms)	Frequency (GHz)	VSWR	Working Voltage (At Sea Level)
U.FL	Ø1.37mm	50	DC-1	1.3 MAX	335V

Product Attributes

Gender	Female to Female
Style	U.FL to U.FL
1st Connector	Gold Plated U.FL Female Plug
2nd Connector	Gold Plated U.FL Female Plug
Features	Shielded
Operating Temperature	-65°C (-85°F) to 150°C (302°F)
BU-4150088050 BU-4150088100 BU-4150088150 BU-4150088200 BU-4150088250 BU-4150088300 BU-4150088500	50 mm (2”) 100 mm (3.9”) 150 mm (5.9”) 200 mm (7.9”) 250mm (9.8”) 300 mm (11.8”) 500mm (19.7”)
RoHS 3 Compliant	