MUELLER® DATASHEET

WI-M-14-XX-@

(Extra Heavy-Duty 14 AWG, UL Recognized, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-14-@ is 14 AWG, 420/0.08 stranded, tinned copper wire with highly flexible 4.7mm diameter silicone jacket.

    - Ratings:

Voltage	1100V
Dielectric Strength	3.2 KV/Min
Spark Test	10 KV
Rated Temperature	-40°C to 180°C
Temperature Rating	FT2
UL Recognition	3640

- Length: The "XX" in the model number indicated length in feet.
  Standard lengths: 10', 25', 30', 50', and 100'

- Color: The "@" in the model number represents color.
  Available colors: -0 Black, -2 Red

Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524