



RoHS
Compliant

BOMcheck.net

Item description

WAGO-I/O-PRO is a programming and visualization tool for control programs, allowing users to develop PLC applications for the programmable fieldbus controller of the WAGO-I/O-SYSTEM 750.

WAGO-I/O-PRO runs in line with the IEC 61131-3 standard, which specifies the requirements for a programming system. The AWL, KOP, FUP, ST and AS programming languages are supported. The optimal programming language can be chosen for each application.

With extensive programming functions, the software readily meets the increasing requirements of control program development; e.g., reusability or modularization.

- Highly efficient translation between programming languages
- Automatic declaration of variables
- Library management

Integrated testing and diagnostics functions also streamline and accelerate the processes involved with implementation of PLC projects.

- Online status indication in the program code
- Offline simulation
- Integrated process visualization



- Recording and graphic presentation of project variables

WAGO-I/O-PRO CAA also offers the option of programming products from other manufactures within the CoDeSys automation alliance in addition to the standard programmable CoDeSys automation alliance products from WAGO.

Data

System requirements

Supported operating systems	Windows XP (SP3 or later) Windows 7
Processor	1 GHz or higher, with 32 bits (x86) or 64 bits (x64)
RAM memory	min. 1 GB RAM (recommended: 2 GB RAM or more)
Hard disk storage	min. 300MByte
Graphics resolution	min. 1024 x 786 (recommended: 1280 x 1024 or higher)
Other system requirements	Open serial interface; CD-ROM and Mouse required

Delivery

Delivery type	Installation file (CD-ROM)
Included	CD-ROM with software and USB communication cable 750-923

Commercial data

Country of origin	DE
GTIN	4045454956776
Customs Tariff No.	85234920009

Downloads

Documentation

Manual

WAGO-I/O-PRO, Programming Tool IEC-61131-3 ; Version 2.3 Programming	May 10, 2012	3.0 MB	Download
WAGO-I/O-SYSTEM 750 IEC-61850 Solution	Jun 25, 2018	19.7 MB	Download
WAGO-I/O-PRO, Programming Tool IEC-61131-3 ; Version 2.3 Visualization	May 10, 2012	920.6 kB	Download
WAGO-I/O-PRO, Programming Tool IEC-61131-3 ; Version 2.3 First steps	May 10, 2012	74.0 kB	Download

Quick-Start Guide

WAGO-I/O-SYSTEM 750 IEC-61850 Solution	Jun 25, 2018	19.7 MB	Download
---	--------------	---------	----------



Programmable fieldbus controller for telecontrol applications IEC 60870 Quick-Start Guide	May 10, 2012	1.5 MB	Download
--	--------------	--------	----------

Bid Text

759-333/000-923 IO, Software	Nov 3, 2017	DOC 29.2 kB	Download
---------------------------------	-------------	----------------	----------

Compatibility Information

WAGO-I/O-PRO, Programming Tool IEC-61131-3 ; Version 2.3 Compatibility notes 759-333	Feb 10, 2015	364.2 kB	Download
---	--------------	----------	----------

Programmable fieldbus controller for telecontrol applications IEC 60870 Interoperability	May 10, 2012	193.6 kB	Download
---	--------------	----------	----------

System Description

Software – General Product Information	Jun 6, 2017	324.7 kB	Download
--	-------------	----------	----------

Engineering-Software

Configuration and Commissioning Software

WAGO-IO-PRO Demo Version / 750, 758 and 762 Series	2.3.9.55 Apr 18, 2018	ZIP 108.3 MB	Download
--	--------------------------	-----------------	----------

Subject to changes.