

BRUMBERG
Light. Since 1873.

B-LIGHT 7-pin mounting rail

Article no. 55003070





IP20 BEG

Tender
7-pin mounting rail, white, Rectangular. Rectangular aluminum trunking for modular quick-assembly continuous-row system for mechanical mounting and electrical supply of modular system components as well as for integrating system-compliant infeed and termination components. Torsion-resistant aluminium profile with optimized profile geometry for high bending and longitudinal stability for industrial, logistics and work areas.trunking length 4,314 mm, trunking width 64.7 mm, height 45.5 mm, trunking width 64.7 mm, height 45.5 mm. With integrated halogen-free through-wiring 2.5 mm², 7-pole (L1, L2, L3, N, PE, DIM+, DIM-), reverse polarity protected plug connection and continuous protective conductor routing. Suitable for switchable and dimmable applications, suitable for direct and suspended mounting (wire/chain). Protection class I according to EN 61140.protection class IP20 according to DIN EN 60529. permissible ambient temperature (ta) -20 °C to +35 °C. Powder-coated surface, color white (RAL 9016). Mounting method: Surface mounting, Material: Aluminium, dimensions profile: length: 4.314 mm x width: 64,7 mm x height: 45,5 mm.

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 14.08.2026 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

B-LIGHT 7-pin mounting rail

Article no. 55003070

Product Benefits

- The Brumberg quick-mounting light strip (SML) consists of torsion-resistant aluminum aluminum trunking as a base.
- For continuous lines in work, storage and production areas.
- Very quick and easy installation thanks to pre-assembled mechanical and electrical couplings and clear system logic.
- Suitable for ceiling surface-mounting and suspended installation.
- Fastening distances/protrusions according to installation instructions.
- Very light and dimensionally stable, in RAL 9016 or RAL 9005, available in 1/2/3 lengths.
- Optionally 7- or 11-pole for defined line connection.
- With integrated halogen-free through-wiring 2.5 mm², 7-pole (L1, L2, L3, N, PE, DIM+, DIM-), reverse polarity protected plug connection and continuous protective conductor routing.
- Ideal for renovations and new builds thanks to its low weight and easy handling.
- Mounting rail length: 4,314 mm
- Mounting rail width: 64.7 mm
- Mounting rail height: 45.5 mm
- Conductor cross-section: 2.5 mm²
- Number of poles: 7-pole
- Housing material: aluminum
- Surface: powder-coated
- Color: white (RAL 9016)
- Permissible ambient temperature: -20 °C to +35 °C
- Protection class I
- Protection class IP20

Article data	
Article no.	55003070
GTIN	4255752527077
Series name	B-LIGHT
Short description	7-pin mounting rail
Material	Aluminium
Colour	white
Type of surface	Smooth
Shape	Rectangular
Length	4,314 mm
Width	64.7 mm
Hight	45.5 mm
Weight	3.95 kg
stamp	ENEC
Conformance	CE, UKCA

Operating technology of the luminaire	
Protection class	I
Degree of protection	IP20
Wire number	7

Mounting technology	
Mounting method	Surface mounting
Place of installation	Ceiling-mounted
Further references	Indoor
Application	Indoor
Suitable for through-wiring	Yes

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 14.08.2026 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

B-LIGHT 7-pin mounting rail
Article no. 55003070

Packing data	
Gross weight	4.1 kg
Length of packaging	4,485 mm
Packaging width	73 mm
Packaging hight	60 mm
Disposal at end of life	This product must not be disposed of with household waste. You are obliged, to dispose of such electrical waste separately. By disposing of electrical waste and other old or defective electronics separately, you support recycling or other forms of re-use. In that way you help to take care and to avoid that harmful substances get into the environment.

Required accessories
Article no.: 55090070 7-pin feed-in box Dimensions: 402 mm x 64.7 mm x 65.7 mm https://www.brumberg.com/fileadmin/products/Datenblatt_55090070_2021_DE.pdf
Article no.: 55095070 End box 237 mm (empty/PE) Dimensions: 237 mm x 64.7 mm x 65.7 mm https://www.brumberg.com/fileadmin/products/Datenblatt_55095070_2021_DE.pdf

Optional accessories
Article no.: 55180070 End cap for rail end Dimensions: 65.9 mm x 64.7 mm x 24.6 mm https://www.brumberg.com/fileadmin/products/Datenblatt_55180070_2021_DE.pdf
Article no.: 55070000 Feed-in plug with 7-pin socket Dimensions: 113 mm x 50 mm x 15 mm https://www.brumberg.com/fileadmin/products/Datenblatt_55070000_2021_DE.pdf
Article no.: 55071000 End feed connector, 7-pin Dimensions: 118 mm x 50 mm x 15 mm https://www.brumberg.com/fileadmin/products/Datenblatt_55071000_2021_DE.pdf

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 14.08.2026 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/