BJZ

SAFE-STAT® stretch film

Technical Datasheet
Creation Date: 30.04.2015

Order-no.: C-205 1178

Stretch film antistatic
Stretch film for manual processing
pink, plain, 1 side adhesive, 1 side smooth

Caution: Surface resistance of 10^9 – 10^{11} Ohm as delivered!

Film characteristics:

		Unit	Value	Test method
Film thickness		µm	20	DIN 53370
Film width		mm	500	DIN 53370
Roll length		m	300	DIN 53370
Core diameter (inside)		mm	50	DIN 53370
Surface resistance		Ohm	10^9 - 10^{11}	Metriso 2000 ESD Meter
Coefficient of friction (COF) non adhesive side		/	0,3 – 0,4	DIN EN ISO 8295, Film / Metal
Tear resistance	Longitudinal (MD)	N	>0,6	Elmendorf DIN 53128
	Lateral (TD)	N	>3,3	Elmendorf DIN 53128

Shelf life:
1. The product should be stored at 15-30°C and 40-70 % RH. Do not expose it to direct sun light or heat.

Handling and storage:
2. Handle the pallets with care. Do not stack them onto each other. Store the rolls in a well ventilated cool place and keep them at a fair distance from irreconcilable and other materials.
3. Do not process, store or open close to open fire, heat or sources of ignition. Do not expose the material to direct sun light.

The stated property standards are based on our current findings and experiences. They do not represent any assurance of particular properties. We reserve the right to make further changes/developments to our products.

The customer has to do their own tests and trials before using our products. Particularly regarding its suitability for a specific purpose.

The same applies to our application-technical information and consultation in speech and writing. In addition, our general terms and conditions apply.

BJZ GmbH & Co. KG
Berwanger Str. 29 • D-75031 Eppingen/Richen
Telefon: +49 -7262-1064-0
Fax: +49 -7262-1063
E-Mail: info@bjz.de
Web: www.bjz.de