

HDC enclosures
HDC 24B XXL MOUNT FRAME**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

General ordering data

Type	HDC 24B XXL MOUNT FRAME
Order No.	1003470000
Version	HDC enclosures, Size: 8, Protection degree: IP68, IP69K, , Screw plug, Standard
GTIN (EAN)	4032248699810
Qty.	1 pc(s).

HDC enclosures

HDC 24B XXL MOUNT FRAME

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	58 mm	Width (inches)	2.283 inch
Height	12 mm	Height (inches)	0.472 inch
Depth	156 mm	Depth (inches)	6.142 inch
Mounting dimension - width	130 mm	Mounting dimension - height	32 mm
Net weight	88 g		

Temperatures

Limit temperature	-50 °C ... 125 °C
-------------------	-------------------

Dimensions

Height of housing B	12 mm	Hole pitch length A2	130 mm
Total length housing	156 mm		

General data

EMC housings	Yes	Housing main material	diecast aluminium
Protection degree	IP68, IP69K		

Version

Design	Standard	Design of locking system	Screw plug
Size	8	Suitable for ModuPlug®	Yes
Top part/bottom part/lid	lower part	Type	Bulkhead (feed-through)

Classifications

ETIM 3.0	EC000437	ETIM 4.0	EC000438
ETIM 5.0	EC000438	ETIM 6.0	EC000437
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-26-12-04	eClass 7.1	27-44-02-02
eClass 8.1	27-44-02-02	eClass 9.0	27-44-02-02
eClass 9.1	27-44-02-02		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN
Engineering Data	EPLAN
Engineering Data	STEP

**HDC enclosures
HDC 24B XXL MOUNT FRAME**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

