BMAX B11 Pro

Ultra-compact AI mini PC with Intel Core Ultra 5

Palm-sized and just 400 g, the B11 Pro packs an Intel Core Ultra 5 115U, 16 GB of LPDDR5 and a 512 GB NVMe SSD into a metallic blue chassis. Its integrated NPU accelerates AI workloads, and Windows 11 Pro comes preinstalled, so it is ready for the office, the home office and multimedia use.



Key features

- **Intel Core Ultra 5 115U:** 8 cores / 10 threads, built for smooth multitasking
- **Integrated NPU (Intel AI Boost)** for AI acceleration, image processing and machine learning
- **16 GB LPDDR5 + 512 GB NVMe SSD** for fast loading and responsiveness
- **Wi-Fi 6 and Bluetooth 5.2** for fast, stable wireless connections
- **"Space Capsule" cooling system** for quiet, efficient heat dissipation
- **Triple-display capability** via HDMI, DisplayPort and USB-C

Technical specifications

Processor	Intel Core Ultra 5 115U (8 cores, 10 threads)
Graphics	Integrated Intel Graphics
AI acceleration	Integrated NPU (Intel AI Boost)
Memory	16 GB LPDDR5 (soldered)
Storage	512 GB NVMe SSD
Storage expansion	1 x M.2 2280 NVMe slot, 1 x SATA port (2.5")
Operating system	Windows 11 Pro (preinstalled)
Wireless	Wi-Fi 6, Bluetooth 5.2
Network	Gigabit Ethernet (RJ45)
Video outputs	1 x HDMI, 1 x DisplayPort, 1 x USB Type-C
USB	4 x USB
Audio	3.5 mm jack
Weight	400 g

In the box

BMAX B11 Pro mini PC • Power adapter • Quick-start guide • Mounting hardware (if required)