

**ESG
SCHS1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

General ordering data

Type	SCHS1
Order No.	0138900000
Version	ESG, Accessories x 17 mm, PVC, Colour: black
GTIN (EAN)	4008190009168
Qty.	1 pc(s).
compatible printer	1324380000

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

Creation date May 27, 2019 8:41:22 PM CEST

ESG
SCHS1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	17 mm	Width (inches)	0.669 inch
Height	1,000 mm	Height (inches)	39.37 inch
Depth	6 mm	Depth (inches)	0.236 inch
Net weight	87 g		

General data

Colour	black	Halogen	No
Material	PVC	Material colour according to resistance code	0
Operating temperature range	-20...80 °C	UL 94 flammability rating	V-0
Width	17 mm		

Classifications

ETIM 3.0	EC001288	ETIM 4.0	EC000761
ETIM 5.0	EC000761	ETIM 6.0	EC001288
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-14-91-29	eClass 7.1	27-14-11-37
eClass 8.1	27-14-11-37	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
------------------	------------------------------

ESG SCHS1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

