Female header

Technical data:

Insulating material:	High temp. Thermoplast UL 94V-0
Contact material:	Phosphor bronze
Rated current:	3 Amp.
Rated voltage:	150 V_{RMS}/V_{DC}
Withstand voltage:	500 V_{RMS} for one minute
Operating temperature:	-40°C to +105°C
Max. soldering temp.:	260°C for 10 seconds

pitch	rows	row distance	orientation	termination
2,54	1		straight	through hole





n = No. of contacts

Pincount: 020

Plating: F = Au

Order code: 904-1-020-0-NFX-XS0-0-0-0-0A79 **Part No.:** 1205010006 6

CS211011_V1_4

MPE-Garry GmbH • Schäfflerstraße 13 • 87629 Füssen • Germany
Phone: +49 (0) 83 62 / 91 56-0 • Fax: +49 (0) 83 62 / 91 56-500 • Email: vk@mpe-connector.de • www.mpe-connector.de