AKL 804 L

Article no.: 40100018 **Color:** black (ähnlich RAL-Nr. 9005)

RUTENBECK
Quality products
Made in Germany



Product Features
Anchoring clamps, housing made of sheet steel, hot galvanized, clamping range 16,5 to 24 mm Ø, tensile strength max. 7,5 kN, for self supporting aerial cables
- Hook diameter: 36mm
- Max. tensile strength 7,5 KN
- housing made of sheet steel, hot galvanized
- clamping jaws and positioning clips made of fibreglass reinforced PA (black)

Features	
General	
Surface	surface finished
Halogen Free	Yes
Statistical goods number	85369095
Country of manufacture	DE
GTIN (EAN)	4043921050699
Dimensions/Weights without packaging	
Length mm	437
Width mm	102
Height mm	53
Net weight piece kg	1,4
Certifications	
RoHS conform	Yes
Logistics Information	
Packaging	box
Packaging unit Quantity	2
Packaging unit Weight kg	2,84
Packaging unit Width mm	102
Packaging unit Height mm	445
Packaging unit Depth mm	68
References	
Similar article	40100012, 40100014, 40100016, 40100020