

Klippon TB (Terminal Box) KTB MOPL 7650 S2N

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image



Abbildung ähnlich

Integrate, expand and customise:

The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Mounting plates

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

Type	KTB MOPL 7650 S2N
Order No.	119390000
Version	Klippon TB (Terminal Box), Mounting plate, Height: 707 mm, Width: 447 mm, Depth: 12 mm, Material: Stainless steel 1.4301 (304), untreated, silver
GTIN (EAN)	4050118028515
Qty.	1 pc(s).

**Klippon TB (Terminal Box)
KTB MOPL 7650 S2N**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	447 mm	Width (inches)	17.598 inch
Height	707 mm	Height (inches)	27.835 inch
Depth	12 mm	Depth (inches)	0.472 inch
Net weight	4,040 g		

General information

Material thickness	1.5 mm	Material	Stainless steel 1.4301 (304)
Surface finish	untreated		

General information on accessories

Material	Stainless steel 1.4301 (304)	Material thickness	1.5 mm
Solder eyelet hole diameter (D)	7 mm	Surface finish	untreated

Classifications

ETIM 4.0	EC002620	ETIM 5.0	EC002620
ETIM 6.0	EC000213	eClass 6.2	27-18-92-61
eClass 7.1	27-18-92-61	eClass 8.1	27-18-92-61
eClass 9.0	27-40-06-39	eClass 9.1	27-18-92-90

Approvals

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

**Klippon TB (Terminal Box)
KTB MOPL 7650 S2N**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

