

**Cutting tools
KT 14**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cutting tools for wires up to 8 mm, 12 mm or 20 mm outer diameter.
The special cutting shape allows for pinch-free cutting of copper and aluminium wires.

General ordering data

| | |
|------------|--|
| Type | KT 14 |
| Order No. | 1157820000 |
| Version | Cutting tools ,Cutting tool for one-hand operation |
| GTIN (EAN) | 4032248945344 |
| Qty. | 1 pc(s). |

**Cutting tools
KT 14**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|--------|-------|
| Length | 215 mm | Width | 66 mm |
| Height | 28 mm | Weight | 320 g |
| Net weight | 324.78 g | | |

Technical data

Version One-hand mechanical

Data, telephone and control cable

Data telephone control cable, max. Ø 14 mm

max. Cutting performance - aluminium cable

| | | | |
|---|--------------------|--|--------------------|
| Single-core aluminium cable, max.(mm ²) | 35 mm ² | Stranded aluminium cable, max (mm ²) | 70 mm ² |
| Stranded aluminium cable, max. (AWG) | 2/0 | Stranded aluminium cable, max. diameter | 14 mm |

max. Cutting performance - copper cable

| | | | |
|-------------------------------|--------------------|-------------------------------------|-----|
| Copper cable - flexible, max. | 70 mm ² | Copper cable - flexible, max. (AWG) | 2/0 |
| Copper cable - solid, max. | 16 mm ² | Copper cable - solid, max. (AWG) | 6 |
| Copper cable - stranded, max. | 35 mm ² | Copper cable - stranded, max. (AWG) | 2 |
| Copper cable, max. diameter | 14 mm | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000005 | UNSPSC | 31-16-31-02 |
| eClass 5.1 | 27-40-02-01 | eClass 6.2 | 21-04-90-90 |
| eClass 7.1 | 27-40-02-01 | | |

Product information

| | |
|---------------------------------|---|
| Descriptive text ordering data | Single-core aluminium cable corresponds to single-wire sector cable |
| Descriptive text technical data | Tool closed |
| Descriptive text accessories | "Single-core aluminium cable" corresponds to single-wire sector cable |

Approvals

Approvals



ROHS Conform

Datenblatt

**Cutting tools
KT 14**


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

 max. 14 mm

 max. 16 mm²

 max. 35 mm²

 max. 70 mm²
