BUSINESS PRODUCTIVITY MONITOR

# PRO MAX 341QPXW14G

PRO MAX 341QPXW14G

## PATH TO THE FUTURE


MSI PRO MP341QPXW14G: Ein 34 Zoll 21:9 QD-OLED-Monitor. Das Ultrawide-Display mit gleichmäßiger Helligkeit ist bereit für Ihren KI-Agenten. Er liefert präzise Farben für die Benutzer und passt perfekt zu MacBook-Setups über die exklusive MSI M-Mate App.




Picture and logos

## SELLING POINTS

- Das aktuellste QD-OLED-Panel der 5. Generation – mit beeindruckender Bildqualität und schneller Reaktionszeit.
- Die MSI M-Mate App ermöglicht eine intuitive Monitorsteuerung und schafft eine einfache Verbindung zwischen deinem Monitor und Mac.
- Mit einem 5-lagigen Tandem-OLED-Panel und EL Gen 3-Technik profitierst du von einer Lichtausbeute bis zu 30 %
- DarkArmor Film sorgt für 40 % tiefere Schwarztöne und eine 2,5-mal kratzfestere Bildschirmoberfläche.
- Uniform Luminance mit HDR Anpassung ermöglicht dir, die HDR-Kurve individuell einzustellen und ein gleichmäßig abgestimmtes HDR-Erlebnis zu genießen.
- MSI OLED Care 3.0 mit AI Care Sensor reduziert das Risiko von OLED Nachbildern und Einbrennen.
- Die integrierten zwei USB-C Anschlüsse mit 98 W und 15 W PD ermöglichen das Laden deiner Geräte direkt am Monitor.
- VisiClarity integriert Anti-Glare Low Reflection, um störendes Licht zu reduzieren und für ein klares, ungespiegeltes Bild mit beeindruckender Tiefe zu sorgen.
- Beeindruckende HDR Darstellung mit VESA DisplayHDR True Black 500.
- Mit einem Spitzenwert von 1300 Nits wird dir ein helles und beeindruckendes HDR Bilderlebnis geboten.
- Kristallklare Bewegung mit VESA ClearMR 8000 Zertifizierung.
- 3 Jahre Schutz vor Burn-in, inklusive Absicherung gegen OLED Einbrennen.




1. Kensington Lock
2. Stromanschluss
3. 2x HDMI™ 2.1 (FRL 12G) (UWQHD@144Hz)
4. 1x DisplayPort 1.4a (HBR3)
5. 1x Typ-C (DP alt.) mit 98W PD
6. 1x Typ-C (DP alt.) mit 15W PD
7. 1x USB 5Gbps Typ-B
8. 4x USB 5Gbps Typ-A
9. 1x Kopfhörerausgang

"2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

BUSINESS PRODUCTIVITY MONITOR

# PRO MAX 341QPXW14G

PRO MAX 341QPXW14G

## SPECIFICATION

| | | |
|---|---|---|
| Model | SKU Number | 9S6-3PFB9T-001 |
| | Entity MKT Name | PRO MAX 341QPXW14G |
| | Part No | 9S6-3PFB9T-001 |
| | Color | ID1/White-White |
| Display | Screen Size | 34" (86.36 cm) |
| | Active Display Area (mm) | 800.06(H) x 337.06(V) |
| | Curvature | Flat |
| | Panel Type | QD-OLED |
| | Resolution | 3440x1440 (UWQHD) |
| | Pixel pitch (mm) | 0.2315(H)x0.2315(V) |
| | Aspect Ratio | 21:9 |
| | Dynamic Refresh Rate technology | Adaptive-Sync |
| | Dynamic Refresh Rate Activated Range | 48~144Hz |
| | HDR (High dynamic range) | VESA DisplayHDR True Black 500 |
| | SDR Brightness (nits) | 300 |
| | HDR Brightness (Peak nits) | 1300 |
| | Contrast Ratio | 1500000:1 |
| | Signal Frequency | 237.2~239 KHz(H) / 48~144 Hz(V) |
| | Refresh Rate | 144HZ |
| | Response Time (GTG) | 0.03ms |
| | View Angles | 178°(H)/178°(V) |
| | NTSC (CIE1976 area percentage/overlap) | 119%/94% |
| | NTSC (CIE1931 area percentage/overlap) | 104.7%/91.8% |
| | sRGB (CIE1976 area percentage/overlap) | 136.4%/99.8% |
| | sRGB (CIE1931 area percentage/overlap) | 147.8%/99.9% |
| | Adobe RGB (CIE1976 area percentage/overlap) | 116.9%/97.4% |
| | Adobe RGB (CIE1931 area percentage/overlap) | 109.6%/94.1% |
| | DCI-P3 (CIE1976 area percentage/overlap) | 108.6%/99% |
| | DCI-P3 (CIE1931 area percentage/overlap) | 109%/99.1% |
| | Rec.709 (CIE1976 area percentage/overlap) | 136.4%/99.8% |
| | Rec.709 (CIE1931 area percentage/overlap) | 147.8%/99.9% |
| | Rec.2020 (CIE1976 area percentage/overlap) | 79.1%/79.1% |
| | Rec.2020 (CIE1931 area percentage/overlap) | 78.2%/78.2% |
| | Surface Treatment | Anti-Glare Low Reflection |
| | Display Colors | 1.07B |
| | Color bit | 10 bits |
| Schnittstellen | USB Type C (DisplayPort Alternate) | 2 |
| | Headphone-out | 1 |
| | USB 3.2 Gen 1 Type A | 4 |
| | USB 3.2 Gen 1 Type B | 1 |
| | Lock type | Kensington Lock |
| | Speaker | 3Wx 2 |
| | HDMI | 2 |
| | HDMI version | 2.1 (FRL 12G) |
| | HDMI HDCP version | 2.3 |
| | DisplayPort | 1 |
| | DisplayPort version | 1.4a (HBR3) |
| | DisplayPort HDCP version | 2.3 |
| Garantie | Warranty | 36M |
| Power | Power Type | Internal Power Board |
| | Power Input | 100~240V, 50/60Hz |
| | Standby-mode Power Consumption (W) | 0.5 |
| | Off-mode Power Consumption (W) | 0.3 |
| | Power Cord Type | C13 |

"2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

| | | |
|---|---|---|
| Zubehör | DisplayPort Cable | 1 |
| | HDMI Cable | 1 |
| | DVI Cable | 0 |
| | USB Type A to Type B Cable | 1 |
| | USB Type C to Type A Cable | 0 |
| | USB Type C to Type C Cable | 1 |
| | Thunderbolt Cable | 0 |
| | VGA Cable | 0 |
| | 3.5mm audio Cable | 0 |
| | 3.5mm combo audio Cable | 0 |
| | 3.5mm Mic Cable | 0 |
| | Power Cord | 1 |
| | AC Adaptor | 0 |
| | Quick Guide | 1 |
| | Warranty Card | 0 |
| | Mouse Bungee Unit | 0 |
| Design | Adjustment (Tilt) | -5° ~ 20° |
| | Adjustment (Swivel) | -30° ~ 30° |
| | Adjustment (Height) | 0 ~ 150 mm |
| | Adjustment (Pivot) | -10° ~ 10° |
| | VESA Mounting | 100x100mm |
| Abmessungen & Gewicht (Verpackung) | Inside Carton Dimension (WxDxH) (cm) | 98.5 x 16.9 x 47.5 |
| | Outer Carton Dimension (WxDxH) (cm) | 100 x 18.4 x 49.8 |
| Barcode Info | EAN | 4711377438001 |

“2026-10-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products.”