

Kisling AG Motorenstrasse 102 CH-8620 Wetzikon

Telefon +41 (0)58 272 01 01 Telefax +41 (0)58 272 01 03 info@kisling.com www.kisling.com

TECHNICAL DATA SHEET ergo 5925

UNIVERSAL GRADE "surface insensitive"

Description

Fast curing standard grade, which is, compare to normal universal grades, insensitive to inactive or difficult surfaces. Although the viscosity is relatively low, the product is able to bond difficult materials, like porous rubber, cardboard, paper, cork or leather.

Certified acc. to **ANSI/NSF Standard 61** for use in commercial and residential potable water systems not exceeding 82° C.

Note: This is a regional approval. Please contact us for more information and clarification.

Physical Properties (liquid product)

Chemical Base: Cyanoacrylicacid-ethylester

Colour: clear/ colourless

Viscosity:20 - 40 mPasat 25°CDensity:1.06 g/cm³DIN 51757Flashpoint:87°CDIN 55213Shelf Life:12 month at room temperature

Fixture Time on:

Aluminium / Aluminium:≤ 60 secondsSBR / SBR - rubber:≤ 5 secondsPolycarbonate / Polycarbonate:≤ 10 secondsEPDM / EPDM - rubber:≤ 7 secondsFinal strength:24 hours

Physical Properties (cured film)

Tensile Shear Strength acc. To EN 1465 on:

Aluminium / Aluminium: > 14 N/mm²
ABS/ ABS: test stripes failed

Tensile Force on round rubber profiles:

EPDM / EPDM - rubber \emptyset 16mm: > 200 N EPDM / EPDM 10 Tage/70°C: > 200 N

Thermal Range: - 30°C up to +80°C

Melting point: + 165°C

WARRANTY INFORMATION - PLEASE READ CAREFULLY

The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that KISLING products are safe, effective, and fully satisfactory for the intended end use. KISLING sole warranty is that the product will meet the KISLING sales specifications in effect at the time of shipment. Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted. KISLING specifically disclaims any other express or implied warranty of fitness for a particular purpose or merchantability. Unless KISLING provides you with a specific, duly signed endorsement of fitness for use, KISLING disclaims liability for any incidental or consequential damages. Suggestions of uses should not be taken as inducements to infringe any particular patent.