

**Industrial Ethernet
IE-S-IP67****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Junction box, design for SnapIn plug-in connectors ver.6
according to IEC 61076-3-106, plastic

General ordering data

Type	IE-S-IP67
Order No.	8808370000
Version	Connecting plug, Junction box, IP67, Cat.6A / Class E _A (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
GTIN (EAN)	4032248505951
Qty.	1 pc(s).

Industrial Ethernet IE-S-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	90 g
------------	------

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Colour	Light Grey	Configuration	Screw-on junction box including RJ45 module with IDC connection
Housing main material	PA 66, UL 94: V-0	Plugging cycles	750
Protection degree	IP67	Sheath diameter, max.	9.5 mm
Sheath diameter, min.	6 mm	Type of mounting	Floor-mounted, for exposed connections, Wall mounting
Wiring	EIA/TIA T568 A, EIA/TIA T568 B		

Standards

Connector standard	IEC 61076-3-106 Var. 6	Certificate No. (GERMLLOYD)	33451-06
--------------------	------------------------	-----------------------------	----------

Technical data RJ45 module

Wiring	EIA/TIA T568 A, EIA/TIA T568 B
--------	--------------------------------

Classifications

ETIM 3.0	EC001264	ETIM 4.0	EC001264
ETIM 5.0	EC001264	ETIM 6.0	EC001121
UNSPSC	43-17-27-10	eClass 5.1	27-25-05-04
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	27-44-03-90
eClass 9.1	27-44-03-90		

Approvals

Approvals



ROHS	Conform
------	---------

Industrial Ethernet IE-S-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	GOST Approval Germanischer Lloyd
Brochure/Catalogue	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Industrial Ethernet IE-S-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing

