

Tools
M-D-STRIPAX +6 MEHA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

General ordering data

| | |
|------------|--|
| Type | M-D-STRIPAX +6 MEHA |
| Order No. | 900350000 |
| Version | Tools, Stripping and cutting tool, Conductor with custom insulation, 7mm |
| GTIN (EAN) | 4008190107109 |
| Qty. | 1 pc(s). |

Tools
M-D-STRIPAX +6 MEHA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|--------|--------|-----------------|------------|
| Width | 82 mm | Width (inches) | 3.228 inch |
| Height | 135 mm | Height (inches) | 5.315 inch |
| Depth | 16 mm | Depth (inches) | 0.63 inch |
| Weight | 110 g | Net weight | 106.38 g |

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Stripping tools

| | | | |
|-------------------------|----------------------------------|-------------------------|--------|
| Cable type | Conductor with custom insulation | Max. conductor diameter | 1.3 mm |
| Min. conductor diameter | 0.2 mm | Stripping length, max. | 7 mm |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000163 | ETIM 4.0 | EC000163 |
| ETIM 5.0 | EC000163 | ETIM 6.0 | EC002109 |
| UNSPSC | 23-17-16-04 | eClass 5.1 | 21-04-03-01 |
| eClass 6.2 | 21-04-38-90 | eClass 7.1 | 21-04-38-90 |
| eClass 8.1 | 21-04-38-90 | eClass 9.0 | 21-04-37-06 |
| eClass 9.1 | 21-04-37-06 | | |

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

Data sheet

Tools
M-D-STRIPAX +6 MEHA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

