

**Pressing tool
HTF RSV 16 WI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for Weidmüller contacts for RSV
and DSTV-HD systems**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF RSV 16 WI
Order No.	9013560000
Version	Pressing tool, Crimping tool for contacts, 26AWG, 16AWG, FoderBcrimp
GTIN (EAN)	4008190161163
Qty.	1 pc(s).

**Pressing tool
HTF RSV 16 WI**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	205 mm	Width (inches)	8.071 inch
Weight	445 g	Net weight	457.48 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	RSV and DSTV-HD	Crimping range, min.	26 AWG
Crimping range, max.	16 AWG		

tool data crimping

Crimping profile 1, min.	26 AWG	Crimping type/profile	FoderBcrimp
Crimping profile 1, max.	24 AWG	Crimping profile 2, min.	22 AWG
Crimping profile 2, max.	20 AWG	Crimping profile 3, min.	22 AWG
Crimping profile 3, max.	20 AWG	Crimping profile 4, min.	16 AWG
Crimping profile 4, max.	18 AWG		

Classifications

ETIM 3.0	EC001396	ETIM 4.0	EC001396
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	27-11-27-20	eClass 5.1	21-05-08-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Approvals

Approvals

**Downloads**

Approval/Certificate/Document of Conformity	Declaration of the Manufacturer
Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 2 PORTFOLIOGUIDE EN
Engineering Data	WSCAD

Data sheet

**Pressing tool
HTF RSV 16 WI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

