

**Pressing tool
CTX CM 1.6/2.5 ZERT**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for turned contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Type	CTX CM 1.6/2.5 ZERT
Order No.	9013690000
Version	Pressing tool, Crimping tool for contacts, 0.14mm ² , 4mm ² , W crimp
GTIN (EAN)	4032248326419
Qty.	1 pc(s).

Data sheet

**Pressing tool
CTX CM 1.6/2.5 ZERT**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Weight	730 g	Net weight	750 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Description of contact

Type of contact	Turned contacts	Crimping range, min.	0.14 mm ²
Crimping range, max.	4 mm ²		

tool data crimping

Crimping profile 1, min.	0.14 mm ²	Crimping type/profile	W crimp
Crimping profile 1, max.	0.5 mm ²	Crimping profile 2, min.	0.75 mm ²
Crimping profile 2, max.	1 mm ²	Crimping profile 3, min.	1.5 mm ²
Crimping profile 4, min.	2.5 mm ²	Crimping profile 5	4 mm ²

Classifications

ETIM 3.0	EC000385	ETIM 4.0	EC000385
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-03-01
eClass 6.2	21-04-06-02	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 6 TOOLS 15/16 EN
--------------------	--

Data sheet

**Pressing tool
CTX CM 1.6/2.5 ZERT**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

