

**Pressing tool  
HTF DFF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Crimping tools for Weidmüller DFF and ZRV contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

**General ordering data**

Type	HTF DFF
Order No.	<a href="#">9014140000</a>
Version	Pressing tool, Crimping tool for contacts, 0.22mm <sup>2</sup> , 2.5mm <sup>2</sup> , FoderBcrimp
GTIN (EAN)	4008190297305
Qty.	1 pc(s).

**Pressing tool  
HTF DFF**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	205 mm	Width (inches)	8.071 inch
Weight	445 g	Net weight	442 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Technical data**

Version Mechanical, without interchangeable inserts

**Description of contact**

Type of contact	Weidmüller DFF	Crimping range, min.	0.22 mm <sup>2</sup>
Crimping range, max.	2.5 mm <sup>2</sup>		

**tool data crimping**

Crimping profile 1, min.	0.22 mm <sup>2</sup>	Crimping type/profile	FoderBcrimp
Wire end ferrules cross-section, min.	0.22 mm <sup>2</sup>	Crimping profile 1, max.	0.35 mm <sup>2</sup>
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Crimping profile 2, min.	0.5 mm <sup>2</sup>
Crimping profile 2, max.	1 mm <sup>2</sup>	Crimping profile 3, min.	1.5 mm <sup>2</sup>
Crimping profile 3, max.	2.5 mm <sup>2</sup>		

**Classifications**

ETIM 3.0	EC001396	ETIM 4.0	EC001396
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	27-11-27-20	eClass 5.1	21-05-08-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

**Approvals**

Approvals

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Declaration of the Manufacturer</a>
Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a> <a href="#">CAT 2 PORTFOLIOGUIDE EN</a>

**Data sheet**

**Pressing tool  
HTF DFF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

