

**Industrial Ethernet
IE-XM-RJ45/RJ45-IP67****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



SnapIn plug-in connectors according to IEC 61076-3-106
ver.6 in plastic, with RJ45 insert

General ordering data

Type	IE-XM-RJ45/RJ45-IP67
Order No.	8808450000
Version	Mounting flange, Coupling flange, straight, Cat.5 (ISO/IEC 11801), IP67
GTIN (EAN)	4032248506033
Qty.	1 pc(s).

Industrial Ethernet IE-XM-RJ45/RJ45-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	42 g
------------	------

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Connection 1	RJ45	Connection 2	RJ45
Description of article		Configuration	and RJ45 module, socket-socket captive lid
	Coupling flange, straight		
Colour	Light Grey	Housing main material	PA 66, UL 94: V-0
Category	Cat.5 (ISO/IEC 11801)	Contact surface	Gold over nickel
Type of mounting	Cabinet, Distribution box	Shielding	360°; shield contact
Protection degree	IP67	Plugging cycles	750

Standards

Connector standard	IEC 61076-3-106 Var. 6, IEC 60603-7-5	Certificate No. (GERMLLOYD)	33451-06
--------------------	---------------------------------------	-----------------------------	----------

Classifications

ETIM 3.0	EC001264	ETIM 4.0	EC001264
ETIM 5.0	EC001264	ETIM 6.0	EC001121
UNSPSC	43-17-27-10	eClass 5.1	27-25-05-04
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	27-44-03-90
eClass 9.1	27-44-03-90		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	GOST Approval Germanischer Lloyd
Brochure/Catalogue	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Creation date May 28, 2019 12:27:38 AM CEST

Industrial Ethernet IE-XM-RJ45/RJ45-IP67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

Dimensioned drawing

