

DMS 3
DMS 3 SET 1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Type	DMS 3 SET 1
Order No.	9007470000
Version	Mains-operated torque screwdriver, 1/4" DIN 3126 Form E6.3, 3
GTIN (EAN)	4008190299224
Qty.	1 pc(s).

Data sheet

**DMS 3
DMS 3 SET 1**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	325 mm	Width (inches)	12.795 inch
Depth	205 mm	Depth (inches)	8.071 inch
Weight	2,004 g	Net weight	1,770 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Charging time	1 h
---------------	-----

Electric screwdriver

Battery voltage	2.4 V	Bit holder	1/4" DIN 3126 Form E6.3
Charger input	230 V AC; 50 Hz; 50 mA	Charger output	2.9 V AC; 1.4 A; 4.1 VA
Charging time	1 h	Idling speed	200 u. 400 min ⁻¹
Rated voltage	2.4 V	Rechargeable batteries	Ni-Mh cells
Torque setting, max.	3 Nm	Torque setting, min.	0.3 Nm
Weight	2,004 g	Weight of charger	700 g
Weight of rechargeable battery	122 g		

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC001395
UNSPSC	27-11-27-20	eClass 5.1	21-05-08-01
eClass 6.2	21-05-08-90	eClass 7.1	21-05-08-04
eClass 8.1	21-05-08-04	eClass 9.0	21-05-21-90
eClass 9.1	21-04-04-17		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD
------------------	-----------------------

Data sheet

DMS 3
DMS 3 SET 1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

