

## Pressing tool HTX LWL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



### Crimping tools for fibre-optic cable connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

Type	HTX LWL
Order No.	<a href="#">9011360000</a>
Version	Pressing tool, Crimping tool for contacts, Hexagonal crimping, Round crimp
GTIN (EAN)	4008190151249
Qty.	1 pc(s).

**Data sheet**

**Pressing tool  
HTX LWL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Weight	415 g	Net weight	415.08 g

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Technical data**

Version	Mechanical, without interchangeable inserts
---------	---

**Description of contact**

Type of contact	Fibre-optic connector
-----------------	-----------------------

**tool data crimping**

Crimping type/profile	Hexagonal crimping, Round crimp	Hexagon AF (A)	3.15 mm
Hexagon spanner width (A 2)	4.85 mm	Crimping station, width (B 1)	6 mm
Crimping station, width (B 2)	6 mm		

**Classifications**

ETIM 3.0	EC001282	ETIM 4.0	EC001282
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-91-14
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

**Approvals**

Approvals



**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
--------------------	--------------------------------------

**Data sheet**

**Pressing tool  
HTX LWL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

