

**Pressing tool  
CTI 6 G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Crimping tools for insulated connectors**

cable lugs, terminal pins, parallel and serial connectors,  
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

**General ordering data**

Type	CTI 6 G
Order No.	<a href="#">9202850000</a>
Version	Pressing tool, Tool for insulated cable connectors, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Oval crimp, Parallel crimp
GTIN (EAN)	4032248517855
Qty.	1 pc(s).

**Data sheet**

**Pressing tool  
CTI 6 G**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	250 mm	Width (inches)	9.842 inch
Weight	747 g	Net weight	689.78 g

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Technical data**

Version	Mechanical, without interchangeable inserts
---------	---

**Description of contact**

Type of contact	Insulated connector	Crimping range, min.	0.5 mm <sup>2</sup>
Crimping range, max.	6 mm <sup>2</sup>		

**tool data crimping**

Crimping profile 1, min.	0.5 mm <sup>2</sup>	Crimping type/profile	Oval crimp, Parallel crimp
Crimping profile 1, max.	1.5 mm <sup>2</sup>	Crimping profile 2, min.	1.1 mm <sup>2</sup>
Crimping profile 2, max.	2.5 mm <sup>2</sup>	Crimping profile 3, min.	2.6 mm <sup>2</sup>
Crimping profile 3, max.	6 mm <sup>2</sup>		

**Classifications**

ETIM 3.0	EC001282	ETIM 4.0	EC001282
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-91-14
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

**Approvals**

Approvals



**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
--------------------	--------------------------------------

**Data sheet**

**Pressing tool  
CTI 6 G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

