

**Pressing tool
HTN 21 M. AN**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	HTN 21 M. AN
Order No.	9014100000
Version	Pressing tool, Crimping tool for contacts, 0.5mm ² , 6mm ² , Indent crimping
GTIN (EAN)	4008190335731
Qty.	1 pc(s).

Data sheet

**Pressing tool
HTN 21 M. AN**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	427 g	Net weight	423.98 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	Uninsulated connection	Crimping range, min.	0.5 mm ²
Crimping range, max.	6 mm ²		

tool data crimping

Crimping profile 1, min.	0.5 mm ²	Crimping type/profile	Indent crimping
Wire end ferrules cross-section, min.	0.5 mm ²	Crimping profile 1, max.	1.5 mm ²
Wire end ferrules cross-section, max.	6 mm ²	Crimping profile 2, min.	1.1 mm ²
Crimping profile 2, max.	2.5 mm ²	Crimping profile 3, min.	2.6 mm ²
Crimping profile 3, max.	6 mm ²		

Classifications

ETIM 3.0	EC001282	ETIM 4.0	EC001282
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-91-14
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------

Data sheet

**Pressing tool
HTN 21 M. AN**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

