

CRIMP-SET STRIPAX PLUS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: STRIPAX-Plus, Stripping tool: STRIPAX-Plus, Crimping range, min.: 0.5, Colour code: Weidmüller
Order No.	9028770000
Type	CRIMP-SET STRIPAX PLUS
GTIN (EAN)	4032248278466
Qty.	1 items
Packaging	Plastic box

CRIMP-SET STRIPAX PLUS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1094 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Technical data

Description of article	Set includes Crimping/ stripping tool for up to 2.5 mm ² and Weidmueller ferrule strips in Weidmueller colour code
------------------------	--

Assortments

Crimping range, max.	2.5 mm ²	Crimping range, min.	0.5 mm ²
Packaging	Plastic box	Stripping tool	STRIPAX-Plus
Crimping tool	STRIPAX-Plus	Colour code	Weidmüller
Number of AEH	2500 pcs.		

Classifications

ETIM 6.0	EC000524	ETIM 7.0	EC000524
ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 9.0	27-40-02-18
ECLASS 9.1	27-40-02-18	ECLASS 10.0	27-40-02-18
ECLASS 11.0	27-40-02-18	ECLASS 12.0	27-40-02-18
ECLASS 13.0	27-40-02-18	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

CRIMP-SET STRIPAX PLUS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H0,5/14 OR BD	Version
Order No.	9004270000	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
GTIN (EAN)	4008190091774	
Qty.	500 ST	
Type	H0,75/14 W BD	Version
Order No.	9004290000	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190006778	
Qty.	500 ST	
Type	H1,0/14 GE BD	Version
Order No.	9004320000	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow
GTIN (EAN)	4008190167523	
Qty.	500 ST	
Type	H1,5/14 R BD	Version
Order No.	9004340000	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190080723	
Qty.	500 ST	
Type	H2,5/14D BL BD	Version
Order No.	9004360000	Wire-end ferrule, Standard, 12 mm, 8 mm, blue
GTIN (EAN)	4008190083397	
Qty.	500 ST	

Stripax plus



Cutting, stripping and crimping tools for connected wire-end ferrules strips

- Cutting
- Stripping
- Crimping
- Automatic feeding of wire end ferrules
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Efficient: only one tool needed for cable work, and thus significant time saved
- Only strips of linked wire end ferrules, each containing 50 pieces, from Weidmüller may be processed. The use of wire end ferrules on reels may lead to destructon.

General ordering data

Type	STRIPAX PLUS 2.5	Version
Order No.	9020000000	Cutting, stripping and crimping tool, Crimping tool for wire-end
GTIN (EAN)	4008190067267	ferrules, 0.5mm², 2.5mm², Trapezoidal crimp
Qty.	1 ST	

CRIMP-SET STRIPAX PLUS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Case**

- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	KOFFER PSC4-01	Version	
Order No.	9028860000	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 ST		