

Tools
multi-stripax GKW LW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

General ordering data

Type	multi-stripax GKW LW
Order No.	9205760000
Version	Tools, Stripping and cutting tool
GTIN (EAN)	4032248790449
Qty.	1 pc(s).

Tools
multi-stripax GWK LW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Height	85 mm	Height (inches)	3.346 inch
Depth	40 mm	Depth (inches)	1.575 inch
Weight	250 g	Net weight	550 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Stripping tools

Stripping length, min.	2 mm	max. cutting capacity, fine-strand	6 mm ²
max. cutting capacity, ribbon	10,2 mm x 4 mm	max. cutting capacity, solid	2.5 mm ²

Classifications

ETIM 3.0	EC000163	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC002109
UNSPSC	30-21-18-01	eClass 5.1	21-04-03-01
eClass 6.2	21-04-38-90	eClass 7.1	21-04-38-90
eClass 8.1	21-04-38-90	eClass 9.0	21-04-37-06
eClass 9.1	21-04-37-06		

Approvals

Approvals



Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)
[CAT 8 SAI 15/16 EN](#)

Data sheet

Tools
multi-stripax GKW LW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

