

**Pressing tool  
HTF AFK 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Similar to illustration

**Crimping tools for Weidmüller DFF and ZRV contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

**General ordering data**

Type	HTF AFK 2.5
Order No.	<a href="#">9201040000</a>
Version	Pressing tool, Crimping tool for contacts, 0.2mm <sup>2</sup> , 2.5mm <sup>2</sup>
GTIN (EAN)	4032248419678
Qty.	1 pc(s).

**Data sheet**

**Pressing tool  
HTF AFK 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Weight	438 g	Net weight	533 g

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Description of contact**

Type of contact	Weidmüller FEKO ZRV	Crimping range, min.	0.2 mm <sup>2</sup>
Crimping range, max.	2.5 mm <sup>2</sup>		

**tool data crimping**

Crimping profile 1, min.	0.2 mm <sup>2</sup>	Crimping profile 1, max.	3.5 mm <sup>2</sup>
Crimping profile 2, min.	0.5 mm <sup>2</sup>	Crimping profile 2, max.	1 mm <sup>2</sup>
Crimping profile 3, min.	1.5 mm <sup>2</sup>	Crimping profile 3, max.	2.5 mm <sup>2</sup>

**Classifications**

ETIM 3.0	EC001396	ETIM 4.0	EC001396
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	27-11-27-20	eClass 5.1	21-05-08-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

**Approvals**

Approvals



**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a> <a href="#">CAT 1 TERM 16/17 EN</a>
--------------------	---

**Data sheet**

**Pressing tool  
HTF AFK 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

