


**Tools**  
**multi-stripax AWG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

**General ordering data**

Type	multi-stripax AWG
Order No.	<a href="#">9202230000</a>
Version	Tools, Stripping and cutting tool, AWG conductors with PTFE and PVC insulation
GTIN (EAN)	4032248486168
Qty.	1 pc(s).

**Tools  
multi-stripax AWG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	250 mm	Width (inches)	9.842 inch
Height	85 mm	Height (inches)	3.346 inch
Depth	40 mm	Depth (inches)	1.575 inch
Weight	250 g	Net weight	520.28 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Stripping tools**

Cable type	AWG conductors with PTFE and PVC insulation	Conductor cross-section (cutting capacity)	6 mm <sup>2</sup>
Copper cable - flexible, max.	6 mm <sup>2</sup>	Stripping length, min.	2 mm
max. cutting capacity, fine-strand	6 mm <sup>2</sup>	max. cutting capacity, ribbon	10,2 mm x 4 mm
max. cutting capacity, solid	2.5 mm <sup>2</sup>		

**Classifications**

ETIM 3.0	EC000163	ETIM 4.0	EC000163
ETIM 5.0	EC000163	ETIM 6.0	EC002109
UNSPSC	23-17-16-04	eClass 5.1	21-04-03-01
eClass 6.2	21-04-38-90	eClass 7.1	21-04-38-90
eClass 8.1	21-04-38-90	eClass 9.0	21-04-37-06
eClass 9.1	21-04-37-06		

**Approvals**

Approvals



**Downloads**

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

**Data sheet**

**Tools**  
**multi-stripax AWG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Example of use**

---

