

## FPC (polycarbonate empty enclosure) FPC 30/40/13 trsp

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Medium-sized polycarbonate housings The FPC series of housings is the next generation of the MPC series. Exhibiting the same material properties, the FPC series has an even wider range of accessories and hence extends the number of potential applications.

Features:

- 6 sizes in 2 versions
- grey or transparent cover
- cover with lead-seal holes
- fixing holes outside the sealed area
- thread for fitting to terminal rails, mounting plates and PCBs
- Comprehensive accessories Weidmüller can manufacture and supply the housings to match customer specifications, fitted with all necessary terminals and cable glands.

### General ordering data

Type	FPC 30/40/13 trsp
Order No.	<a href="#">9535760000</a>
Version	FPC (polycarbonate empty enclosure), Empty enclosure, Height: 300 mm, Width: 400 mm, Depth: 132 mm, Material: Polycarbonate, Light Grey, Transparent
GTIN (EAN)	4032248007158
Qty.	1 pc(s).

## FPC (polycarbonate empty enclosure) FPC 30/40/13 trsp

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

Width	400 mm	Width (inches)	15.748 inch
Height	300 mm	Height (inches)	11.811 inch
Depth	132 mm	Depth (inches)	5.197 inch
Weight	2,199 g	Net weight	2,620 g

### Cable glands, right

M12	38	M16	21
M20	12	M25	8
M32	3	M40	3
M50	2	M63	2

### Cable glands, top/bottom

M12	56	M16	30
M20	18	M25	12
M32	5	M40	4
M50	4	M63	3

### General information

Areas of use	Building systems and technology, Transportation, Packaging industry, Machine construction	Material	Polycarbonate
Seal material	Polyurethane	Operating temperature, min.	-50 °C
Operating temperature, max.	130 °C	Protection degree	IP66, IP67
Enclosure attachment	Holes 7.5 mm	Lid attachment	4 polyamide crosshead screws
Integral fixing	thanks to self-tapping screws		

### General information on accessories

Material	Polycarbonate
----------	---------------

### horizontal assembly

WDU 10 / ZDU 10	1x30	WDU 16 / ZDU 16	1x25
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x59	WDU 35 / ZDU 35	1x19
WDU 4 / ZDU 4	1x49	WDU 6 / ZDU 6	1x37

### vertical assembly

WDU 10 / ZDU 10	3x20	WDU 16 / ZDU 16	3x17
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x40	WDU 35 / ZDU 35	3x12
WDU 4 / ZDU 4	3x33	WDU 6 / ZDU 6	3x25

**Data sheet**

**FPC (polycarbonate empty enclosure)  
FPC 30/40/13 trsp**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Classifications**

ETIM 3.0	EC000058	ETIM 4.0	EC000058
ETIM 5.0	EC000058	ETIM 6.0	EC000261
UNSPSC	31-26-15-02	eClass 5.1	27-14-91-07
eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
eClass 8.1	27-14-91-07	eClass 9.0	27-18-01-01
eClass 9.1	27-18-92-90		

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**FPC (polycarbonate empty enclosure)  
FPC 30/40/13 trsp**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

