

**Testing tools**  
**VT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

**General ordering data**

Available until	1970-01-01
Type	VT
Order No.	<a href="#">9918950000</a>
Version	2-pole voltage tester, No
GTIN (EAN)	4032248405831
Qty.	1 pc(s).

**Data sheet**

**Testing tools  
VT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	190 mm	Width (inches)	7.48 inch
Height	21 mm	Height (inches)	0.827 inch
Depth	55 mm	Depth (inches)	2.165 inch
Weight	115 g	Net weight	115 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Measuring and testing devices**

AC voltage display	12, 50, 120, 230, 400, 690 V	AC voltage measuring range	12-690 V
Continuity test	No	DC voltage display	12, 50, 120, 230, 400, 690 V
DC voltage measuring range	1000 V	Display	LED
Frequency range, max.	65 Hz	Frequency range, min.	0 Hz
Insulation test	5 kV	Measuring range category	CAT III 600 V, CAT IV 300 V
Peak voltage resistance	5 kV	Protection degree	IP64
Rated voltage, max.	690 V AC/DC	Rated voltage, min.	12 V AC/DC
Tested and approved according to	EN/ IEC 61010, EN 61243-3 2010	Working temperature, max.	55 °C
Working temperature, min.	-15 °C		

**Classifications**

ETIM 3.0	EC000494	ETIM 4.0	EC000494
ETIM 5.0	EC000494	ETIM 6.0	EC000494
UNSPSC	41-11-36-37	eClass 5.1	27-20-03-08
eClass 6.2	27-20-03-08	eClass 7.1	27-20-03-08
eClass 8.1	27-20-03-08	eClass 9.0	27-20-03-08
eClass 9.1	27-20-03-08		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">9918950000_DECLARATION_OF_CONFORMITY.pdf</a>
Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
User Documentation	<a href="#">Manual</a>

**Data sheet**

**Testing tools**  
**VT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

